

Optical Parallels SERIES 157

- Designed to inspect parallelism and flatness of measuring faces of micrometers. For details, refer to "Quick Guide to Precision Measuring Instruments" on page B-73.
- Each set consists of 4 sizes to aid in testing parallelism at various angular positions of the micrometer spindle.



157-903

SPECIFICATIONS

Order No.	Range of micrometer to be checked (mm)	Sizes of parallels included in set (mm)	Diameter (mm)	Flatness (µm)	Parallelism (µm)	Rer
157-903	0 - 25	12.00, 12.12, 12.25, 12.37	ø30	0.1	0.2	
157-904	25 - 50	25.00, 25.12, 25.25, 25.37	050	0.1	0.2	
Inch	-					

Order No.	Range of micrometer to be checked (in)	Sizes of parallels included in set (in)	Diameter (mm)	Flatness (µm)	Parallelism (µm)	Remarks (mm)
157-901	0 - 1	0.5000, 0.5062, 0.5125, 0.5187	ø30	0.1	0.2	For 25
157-902	1 - 2	1.0000, 1.0062, 1.0125, 1.0187				For 50

* Also available individually, using the following Order No.

Metric		Metric	
Order No.	Thickness (mm)	Order No.	Thickness (mm)
157-101	12.00	157-105	25.00
157-102	12.12	157-106	25.12
157-103	12.25	157-107	25.25
157-104	12.37	157-108	25.37
Inch		Inch	
Order No.	Thickness (in)	Order No.	Thickness (in)
157-109	0.5000	157-113	1.0000
157-110	0.5062	157-114	1.0062
157-111	0.5125	157-115	1.0125
157-112	0.5187	157-116	1.0187

Optical Flats SERIES 158

• Used for inspecting the flatness of very flat surfaces. For details, refer to "Quick Guide to Precision Measuring Instruments" on page B-73.



SPECIFICATIONS

Metric			
Order No.	Thickness (mm)	Diameter (mm)	Flatness grade (µm)
158-117	12	45	0.2
158-118	IZ	45	0.1
158-119	15	60	0.2
158-120	15	00	0.1

Inch	I		
Order No.	Thickness (in)	Diameter (in)	Flatness grade (in)
158-122	0.5	1.8	0 000004
158-124	0.6	2.4	0.000004





marks (mm For 25 For 50